Planetary | E24189-138BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

In a galaxy of light, ribbed and tinted glass is supported by swooping arcs of circular tubes. The Gold frame supports glass globe shades colored in Amber and Smoke tints that encase LED lamps provided. The single pendant has an over-sized spiraling glass shade in either Amber or Smoke, with a dome of light within and Matte Black components. Two configurations of wall sconces pair perfectly with the collection.



MEASUREMENTS

DIMENSION	: 9.75" L x 9.75" W x 10.5" H
MAX OAH	: 132" OAH
CANOPY	: 6" W x 1.5" H x 6" L
HANGING WEIGHT	: 2.6 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 800 Rated (720 Del.)
BULB	: 1 x 11W LED DC Integrated , 11W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

GLASS

Smoke 138

MATERIAL

Aluminum, Steel, PC, Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

SLOPE: 15
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com