



**50+ YEARS IN
BUSINESS**

**100% INDEPENDENT
PRIVATELY OWNED**

**15,000 +
PRODUCTS**

**2 MILLION SQ. FT
OF INVENTORY**

**6 WAREHOUSE
LOCATIONS**

SATCO LED lamps offer one of today's largest selections of T24/T20 LED products — providing solutions for the commercial, industrial and residential markets.

We bring quality, value and design to every product we create. With advancing technology, we improve performance, energy savings, safety, ease of installation and maintenance, and overall satisfaction.

We are your partners in success — from convenient packaging options and retail support to inventory supply.

SATCO is the lighting solution you can count on for the products you can rely on!

LED FILAMENT LAMPS



Features:

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Dimmable
- Damp location
- Approved for totally enclosed fixtures ^
- c-UL-us listed
- ENERGY STAR certified
- 3 Year warranty





S14
*Non-dimmable



T6



BT15



ST19



T10 / 5"



BT15

ST19

T6

T9 / 5"



S8021

S8022

S8023

S8024

S8025

S8026



LED String Light Replacement Lamps Sold in 4 Packs



Item	Description	W	V	Bulb Shape	Base	Finish	CCT	Lm	CRI	MOL (in.)	MOD (in.)	Life (hrs.)	UPC	Pack
BT15														
S8559*	5.5BT15/LED/E26/27K/120V	5.5	120	BT15	E26	CL	2700K	500	90	3.63	1.88	15K	045923085598	24/6
S11378	8BT15/LED/927/CL/120V	8	120	BT15	E26	CL	2700K	800	90	4.30	1.81	15K	045923113789	24/6
S11379	8BT15/LED/927/SW/120V	8	120	BT15	E26	SW	2700K	800	90	4.30	1.81	15K	045923113796	24/6
ST19														
S8554*	5.5ST19/CL/LED/E26/27K/120V	5.5	120	ST19	E26	CL	2700K	500	90+	5.50	2.38	15K	045923085543	24/6
S11382	8ST19/LED/930/CL/120V	8	120	ST19	E26	CL	3000K	800	90	4.90	2.28	15K	045923113826	24/6
Tubular LED Filament														
S8555*	2.5T6/LED/CL/27K/E12/120V	2.5	120	T6	E12	CL	2700K	180	90	3.19	0.75	15K	045923085550	24/6
S8556*	4T10/LED/E26/27K/120V	4	120	T10	E26	CL	2700K	350	90	5.00	1.25	15K	045923085567	24/6
S11381*	4.3T10/LED/930/CL/120V	4.3	120	T10	E26	CL	3000K	350	90	5.30	1.25	15K	045923113819	24/6
S11380	8T9/LED/927/CL/120V	8	120	T9	E26	CL	2700K	800	90	5.00	1.14	15K	045923113802	24/6
LED String Light Replacement Lamps														
S8021*	1W S14 REPLACEMENT LAMPS/4PK	1	120	S14	E26	CL	2700K	100	80	3.43	1.81	15K	045923080210	24/4
S8022*	1W/LED/S14/RED/120V/ND/4PK	1	120	S14	E26	RED	N/A	40	N/A	3.43	1.81	15K	045923080227	24/4
S8023*	1W/LED/S14/BLUE/120V/ND/4PK	1	120	S14	E26	BLUE	N/A	15	N/A	3.43	1.81	15K	045923080234	24/4
S8024*	1W/LED/S14/GREEN/120V/ND/4PK	1	120	S14	E26	GRN	N/A	30	N/A	3.43	1.81	15K	045923080241	24/4
S8025*	1W/LED/S14/YELLOW/120V/ND/4PK	1	120	S14	E26	YLW	N/A	120	N/A	3.43	1.81	15K	045923080258	24/4
S8026*	1W/LED/S14/ORANGE/120V/ND/4PK	1	120	S14	E26	ORNG	N/A	90	N/A	3.43	1.81	15K	045923080265	24/4

*Non-Dimmable

^ See warranty for details at www.satco.com