



jalas® CLEAN 3520

ASTM F2413-18 M/I/C/SD 35/PR EN ISO 20345:2022 S2, LG

Learn more

Comfort and durability meet in an easy-clean safety shoe with (S2) protection in striking white design. The PU-coated leather upper supports and stabilises feet while the ventilating inner sole keeps them cool. An oil-resistant PU outer sole provides fantastic grip in slippery conditions, while the JALAS® aluminium toe cap and double impact protection zones in PORON® XRD® keep feet safe both indoors and out.

CHARACTERISTICS

- Highest level of protection
- Excellent grip
- Perfect fit
- Extra comfortable
- Excellent shock absorption

FUNCTIONS

- Oil-resistant outsole
- Anti-static properties
- Polstered shaft edge
- Ventilating insole
- Double shock absorption zones
- Conforms with IEC 61340-5-1 (ESD)
- Water repellent

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF
Toe injuries, Antistatic

PRIMARY ENVIRONMENTS OF USE
Outdoors, Indoors

PRIMARY AREAS OF USE
Laboratory work, Paint spraying work

SPECIFICATION
TYPE Safety footwear, Loafers
CATEGORY Cat. II
FITTING Regular
COLLECTION Clean
UPPER MATERIAL PU-coated leather
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester, polyamide
INSOLE JALAS 8103 FX2 Pro-X
INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in PORON® XRD®
OUTSOLE MATERIAL PU outsole
FASTENING Elasticated opening
COLOUR White
NET WEIGHT, (SIZE 42) 0.98 kg

COMPLIANCE
CE Cat. II

EAC TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

EN ISO 20345:2022
S2, LG

FEATURES
- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- Water repellent

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
36	3	4	5	3520-36	6408487431104
37	4	5	6	3520-37	6408487431111
38	5	5.5	6.5	3520-38	6408487431128
39	6	6.5	7.5	3520-39	6408487431135
40	6.5	7.5	8.5	3520-40	6408487431142
41	7	8	9	3520-41	6408487431159
42	8	9	10	3520-42	6408487431166
43	9	9.5	11	3520-43	6408487431173
44	10	10.5	11.5	3520-44	6408487431180
45	10.5	11	12.5	3520-45	6408487431197
46	11	12	13	3520-46	6408487431203
47	12	13	14	3520-47	6408487431210

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.