

## HOW TO READ PRODUCT INFORMATION – COMPACT FLUORESCENT

Nominal Wattage	Bulb Shape	MOL (in)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Avg rated life (hrs)	CCT	CRI	Approx. Lumens at 25°C/77°F	Notes
-----------------	------------	----------	------	----------------	-----------------------	---------	----------------------	-----	-----	-----------------------------	-------

<b>Bulb</b>	Describes the shape of the bulb.
<b>Base</b>	Base designations for compact fluorescent lamps are the NEMA designations.
<b>Symbols &amp; Footnotes</b>	Most symbols and footnotes that apply to a specific product will appear in this space. The explanations of the symbols and footnotes are at the end of the compact fluorescent section.
<b>Ordering Abbreviation</b>	A text description of the lamp. Please see below for an example and explanation of the code.
<b>NEMA Generic Designation</b>	Designation assigned by NEMA (National Electrical Manufacturers Association).
<b>CCT</b>	Correlated Color Temperature. Measured in degrees Kelvin (K).
<b>CRI</b>	Color Rendering Index. A numbering system for rating the relative color rendering quality of a light source compared to a standard.
<b>Initial Lumens</b>	Initial lumens are measured when the lamp has been operating for 100 hours. Compact Fluorescent lamp lumens are measured at 25°C (77°F) and 35°C (95°F).

### How to Read Ordering Abbreviations

CF23EL/MICRO/827/LS/RP2


CF	Compact Fluorescent
23	Nominal lamp wattage
EL	Electronic Lamp
MICRO	Type of bulb
827	'8' denotes CRI in the 80's. '27' 2700K CCT
LS	Living Spaces™
RP2	Retail Two Pack

### LAMP DISPOSAL LABELING

The following information appears on the packages of fluorescent lamps.



For weight and measurement information, please visit [www.sylvania.com](http://www.sylvania.com)



### DULUX® T 2-Pin ECOLOGIC® Triple-Tube Compact Fluorescent Lamps

Nominal Wattage	Bulb Shape	MOL (in)	MOL (mm)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Average Rated Life (hrs)	CCT (K)	CRI	Approx. Lumens Initial (Mean) at 25°C/77°F	Notes
26	T (T4)	5	106	GX24D-3	20454	CF26DT/827/ECO	50	12000	2700	82	1800 (1620)	1,3,5,9,11

### DULUX L SUPERSAVER® ECOLOGIC® Compact Fluorescent Lamps

Nominal Wattage	Bulb Shape	MOL (in)	MOL (mm)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Average Rated Life (hrs)	CCT (K)	CRI	Approx. Lumens Initial (Mean) at 25°C/77°F	Notes
28	L (T5)	22.4	570	2G11	20518	FT40DL/28W/830/SS/ECO	10	20000	3000	82	2800 (2410)	1,2,4,5,9,12
					20519	FT40DL/28W/835/SS/ECO	10	20000	3500	82	2800 (2410)	1,2,4,5,9,12
					20488	FT40DL/28W/841/SS/ECO	10	20000	4100	82	2800 (2410)	1,2,4,5,9,12
25	L (T5)	22.4	570	2G11	20117	FT40DL/25W/835/SS/ECO	10	20000	3500	82	2500 (2300)	1,2,4,5,9,12
					20118	FT40DL/25W/841/SS/ECO	10	20000	4100	82	2500 (2300)	1,2,4,5,9,12

### DULUX L ECOLOGIC Compact Fluorescent Lamps

Nominal Wattage	Bulb Shape	MOL (in)	MOL (mm)	Base	Product Number	Ordering Abbreviation	Pkg Qty	Average Rated Life (hrs)	CCT (K)	CRI	Approx. Lumens Initial (Mean) at 25°C/77°F	Notes
18	L (T5)	9	225	2G11	20587	FT18DL/835/ECO	10	12000	3000	82	1250 (1075)	1,2,4,5,9
					20588	FT18DL/835/ECO	10	12000	3500	82	1250 (1075)	1,2,4,5,9
					20589	FT18DL/841/ECO	10	12000	4100	82	1250 (1075)	1,2,4,5,9
18	L (T5)	10.5	268	2G11	20595	FT18DL/830/RS/ECO	10	20000	3000	82	1120 (963)	1,2,4,5,9
					20594	FT18DL/835/RS/ECO	10	20000	3500	82	1250 (1075)	1,2,4,5,9
					20593	FT18DL/841/RS/ECO	10	20000	4100	82	1250 (1075)	1,2,4,5,9
24	L (T5)	12.9	320	2G11	20597	FT24DL/830/ECO	10	12000	3000	82	1800 (1548)	1,2,4,5,9
					20580	FT24DL/835/ECO	10	12000	3500	82	1800 (1548)	1,2,4,5,9
					20596	FT24DL/841/ECO	10	12000	4100	82	1800 (1548)	1,2,4,5,9
36	L (T5)	16.6	415	2G11	20581	FT36DL/830/ECO	10	12000	3000	82	2900 (2495)	1,2,4,5,9
					20582	FT36DL/835/ECO	10	12000	3500	82	2901 (2495)	1,2,4,5,9
					20583	FT36DL/841/ECO	10	12000	4100	82	2902 (2495)	1,2,4,5,9
40	L (T5)	22.4	570	2G11	20584	FT40DL/830/RS/ECO	10	15000	3000	82	3150 (2710)	1,2,4,5,9
					20585	FT40DL/835/RS/ECO	10	15000	3500	82	3150 (2710)	1,2,4,5,9
					20586	FT40DL/841/RS/ECO	10	15000	4100	82	3150 (2710)	1,2,4,5,9
					20576	FT40DL/850/RS/ECO	10	20000	5000	82	3150 (2710)	1,2,4,5,9
50	L (T5)	22.6	570	2G11	20278	FT50DL/835/RS/ECO	10	14000	3500	82	4300 (3655)	1,2,4,5,9
					20276	FT50DL/841/RS/ECO	10	14000	4100	82	4300 (3655)	1,2,4,5,9
55	L (T5)	21.1	535	2G11	20590	FT55DL/830/ECO	10	12000	3000	82	4800 (4143)	1,2,4,5,9
					20591	FT55DL/835/ECO	10	12000	3500	82	4800 (4143)	1,2,4,5,9
					20592	FT55DL/841/ECO	10	12000	4100	82	4800 (4143)	1,2,4,5,9