Project / Job Name:

Location:

Fixture Type:

Notes:



67-395 - Remote Emergency Light; Chicago Approved; White Housing; Single Head; 6 Vdc 1.5 W

DAMP LOCATION | c UL us LISTED | RoHS COMPLIANT | 50,000 HOURS

GENERAL

Company	SATCO
EA Height	5.31
EA Width	5.12
EA Length	5.12
Diameter	4.94
Material	Steel
Fixture Type	Exit Sign
Status	Active
Style	Utility
CCT Selectable	No
Wattage Selectable	No
Finish Family	White
Amps	0.250A
Lens Finish	Frosted
Lens Material	Acrylic
SDS Class	LED_Fixture
Indoor Outdoor	Indoor
Product Technology	LED
Serviceable Battery	No
Battery Indicator	No
Digital Display	No

ELECTRICAL

CCT (Kelvin Temp)	5700K
Hours Rated	50000
Beam Angle (degree)	20
Color Temp	Daylight
CRI	80+
Operating Temp	+41F to +113F (+5C to +45C)
Lumens	200L
Volts	6V
Watts	1.5W
Connection	Hardwire

PHYSICAL

Lamp Base	Integrated
Finish	Gloss White
ANSI Base	Integrated
Lamp Type	Integrated LED
Fixture Shape	Round
Mounting Procedure	Ceiling, Wall

ADDITIONAL INFO

Warranty	2-Years

PACKAGING

UPC	045923415807
Case Cube	1.1009
Case Height	11.02
Case Length	15.94
Case Quantity	12
Case UPC	10045923415804
Case Weight	10.58
Case Width	10.83
EA Cube	0.0806
EA Height	5.31
EA Length	5.12
EA Quantity	1
EA Weight	0.69
EA Width	5.12
Pack Type	Kraft Box
Web Length	4.74
Web Width	4.94

COMPLIANCE

CA Prop 65	Lead
Dark Sky Rated	No
IP Rating	IP40
Location Rating	Damp
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cULus - Listed
California Ban	Lawful for sale
Energy Star Certified	No
Title 20	Exempt
T24/JA8 Compliant	No
US State Ban	CA

© Satco Products, Inc.
All rights reserved 2026