



TEGERA® 777

Learn more

A PRECISION GLOVE WITH SMOOTH DIPPING

Thin work glove for delicate tasks. Superb dexterity and tactility thanks to the ultra thin 18G knitting technology. Thin PU coating on palm provides better grip and abrasion protection. Dark blue and black colours help mask dirt and extends product use. Each pair comes with a hook which makes them easy to display.

CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Good grip
- Extra comfortable

FUNCTIONS

- Ultra thin
- Super soft

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Blisters, Grazes, Contact with dirt, Drying out

PRIMARY ENVIRONMENTS OF USE

Dry environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE

Fine assembly

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Building and construction, Electrical equipment manufacturing, Electricity and gas supply, Facility management services, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Transport equipment manufacturing, Warehousing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Precision work gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 18
LINING MATERIAL Nylon
LENGTH 220-270 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR Blue
PAIRS PER: BUNDLE/CARTON 6/120
DISPLAY TYPE Hook with hangtag
DIPPING Palm-dipped
DIPPING MATERIAL PU
CUFF STYLE Rolled edges
CUFF MATERIAL Textile
INNER MATERIAL SPECIFICATION Nylon
OUTER MATERIAL SPECIFICATION Polyurethane

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018
2110X

ANSI 3 ABR

SIZE		ARTICLE NUMBER	EAN
5	XXS	777-5	7340118325392
6	XS	777-6	7340118320786
7	S	777-7	7340118320809
8	M	777-8	7340118320823
9	L	777-9	7340118320847
10	XL	777-10	7340118320748
11	XXL	777-11	7340118320762

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.