Entanglement | E21250-20BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A network of wire and crystal are suspended within a box frame illuminated from above. The light panel above highlights the iridescence of the crystal while providing ample illumination to the space below.



MEASUREMENTS

DIMENSION	: 19.75" L x 19.75" W x 8" H
MAX OAH	: 8" OAH
CANOPY	: 15.75" W x 1.5" H x 15.75" L
HANGING WEIGHT	: 13.2 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,200 Rated (1,500 Del.)
BULB	: 1 x 36.5W LED DC Integrated , 36W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 30-35-40K

FINISHES OPTION

Black (BK)

GLASS

Crystal 20

MATERIAL

Steel, Crystal

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com