

HOM115GFICP

Mini circuit breaker, Homeline, 15A, 1 pole, 120VAC, 10kA AIR, ground fault class A, plug in, UL



Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	15 A
Certifications	UL Listed
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number of Poles	1P
Short Circuit Current Rating	10 kA
Number of Spaces	1
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	HACR rated
Electrical Connection	Screw clamp terminals
Wire Size	AWG 14...AWG 10 aluminium/copper)1
Type of Packing	Consumer packaging

Complementary

Tightening torque	36.29 lbf.in (4.1 N.m) 0.00...0.01 in ² (2.5...6 mm ²) (AWG 14...AWG 10)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)
Net Weight	0.66 lb(US) (0.30 kg)

Environment

Ambient Air Temperature for Operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	01319-HOMELINE GRD. FAULR BRKRS
Discount Schedule	CPH
GTIN	047569071096
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.20 in (3.048 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	7.90 in (20.066 cm)
Package 1 Weight	10.40 oz (294.835 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	3
Package 2 Height	4.70 in (11.938 cm)
Package 2 Width	4.10 in (10.414 cm)

Package 2 Length	8.40 in (21.336 cm)
Package 2 Weight	33.60 oz (952.543 g)
Unit Type of Package 3	PAL
Number of Units in Package 3	504
Package 3 Height	40.00 in (101.6 cm)
Package 3 Width	40.00 in (101.6 cm)
Package 3 Length	48.00 in (121.92 cm)
Package 3 Weight	353.00 lb(US) (160.118 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Halogen content performance	Halogen free product

Contractual warranty

Warranty	Lifetime
----------	----------