



Technical Data

Color	Gray
Sizes Available	OS
Packaging	Bagged Pair
Packed	200/Case
Case Dimensions (in)	19.69 x 11.81 x 9.84
Case Weight (lbs)	8.82
Country of Origin	China
Lens	Indoor Outdoor
Frame Style	Rimless
Lens Color	Silver
Lens Coating	, Anti-Scratch
Bridge	Rubber
Certifications	ANSI Z87.1

UVEX® A800

Rimless Gray Safety Glasses With Silver Anti-Scratch, Hard Coat, Mirror, Indoor-Outdoor Lens

- Temples feature aggressive sports styling and soft, padded inserts with extra flex built in for more comfort
- Soft nosepiece conforms to various nose bridge shapes for added comfort and a non-slip fit
- 9 Base polycarbonate hard coat lenses provide a 180 degrees field of distortion-free vision
- Extra "flex" built into the temple for increased tension control
- Provides 99. 9% UV protection
- Meets ANSI Z87.1+

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
A804	Gray	I/O	Silver	AS	040025108589		
A804-EH	Gray				198987170295	10198987170292	20198987170299

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated