




TEGERA® 84301

Learn more

OUR THINNEST DISPOSABLE GLOVE

Thin disposable high-quality glove, only 0,06 mm/2,3 mils nitrile and yet very durable. Approved for handling food stuffs. Latex free and phthalate-free. Touchscreen functionality, no need to take the gloves off when using your smartphone. For precision work. 200 pieces/box. 10 boxes/carton.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible

FUNCTIONS

- Splash protection against chemicals
- Approved for handling foodstuffs
- For touchscreen
- Waterproof
- Thin

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Risk of infection, Contact with dirt, Contact with damp, Contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Chemical risk environments, Microbiological risk environments, Disposable use, Moist environments, Oily and greasy environments, Dirty environments

PRIMARY AREAS OF USE

Fine assembly, Food handling, Laboratory work

PRIMARY INDUSTRIES OF USE

Food and beverage processing, Accommodation and food service (HoReCa), Public safety, security and defence

TYPE OF WORK

Light weight

CHEMICAL RESISTANCE

According to EN16523-1:2015. For details, please contact Ejendals.

SPECIFICATION

TYPE Disposable gloves - General protection
CATEGORY Cat. III
THICKNESS 0,06 mm
LENGTH 240 mm
INSIDE Non powder
GRIP DESIGN Extra fingertip grip
COLOUR Blue
QUANTITY PER PACK 200 Pieces
PACKS PER: BUNDLE/CARTON Not sold in bundle/10
AQL 1.5
DISPLAY TYPE Box
DIPPING MATERIAL Nitrile

COMPLIANCE

CE 0598

EAC

TP TC 019:2011

EN ISO 21420:2020

EN ISO 374-1:2016/Type B JKT

EN ISO 374-5:2016 Virus

FDA compliant material

FEATURES

For touchscreen

Waterproof

General Protection

TEST ACCORDING TO EN ISO 374-1:2016

Tested chemical	J	K	T
Permeation level	6	6	6
Degradation %	48,8	-4,4	7,6

SIZE		ARTICLE NUMBER	EAN
7	S	84301-7	7340118301150
8	M	84301-8	7340118301174
9	L	84301-9	7340118301198
10	XL	84301-10	7340118301112
11	XXL	84301-11	7340118301136

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.