Alumilux Line | E41342-ABZ


Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION



MEASUREMENTS

DIMENSION	: 2.75" W x 18" H x 1.5" Ext
BACK PLATE	: 4.5" W x 4.5" H
HANGING WEIGHT	: 7.92 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 900 Rated (540 Del.)
BULB	: 1 x 9W LED PCB Integrated , 9W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Architectural Bronze (ABZ)
Black (BK)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com