



Project / Job Name: \_\_\_\_\_

Location: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Notes: \_\_\_\_\_

**S14226** - 3.5 Watt A19 LED; 2000K CCT; Medium Base; Clear Glass; Amber Coil Filament; Dimmable; 120 Volt



**GENERAL**

|                           |  |
|---------------------------|--|
| Company                   | SATCO                                  |
| EA Height                 | 4.79                                   |
| EA Width                  | 2.58                                   |
| EA Length                 | 2.58                                   |
| Dimmable Text             | Forward or Reverse Phase; Line Voltage |
| Lamp Filament             | Spiral                                 |
| Material                  | Glass                                  |
| Fixture Type              | Miniature                              |
| Status                    | Active                                 |
| Surge Protection          | Built-in surge protection - 2.5KV      |
| Total Harmonic Distortion | <70%                                   |
| CCT Selectable            | No                                     |
| Wattage Selectable        | No                                     |
| Finish Family             | Clear                                  |
| Amps                      | 0.050A                                 |
| Lens Material             | Glass                                  |
| Operating Position        | Universal                              |
| Power Factor              | >0.7                                   |
| SDS Class                 | LED_Lamp                               |
| Indoor Outdoor            | Indoor and Outdoor                     |
| Product Technology        | LED                                    |
| Incandescent Equivalent   | 25W                                    |

**ELECTRICAL**

|                     |                             |
|---------------------|-----------------------------|
| CCT (Kelvin Temp)   | 2000K                       |
| Dimmable            | Yes-Dimmable                |
| Hours Rated         | 15000                       |
| Beam Angle (degree) | 300                         |
| Color Temp          | Warm White                  |
| CRI                 | 90+                         |
| Dimming Type        | Linear Dimming, Phase cut   |
| Operating Frequency | 60Hz                        |
| Operating Temp      | -25C (-13F) to +40C (+104F) |
| Lumens              | 300L                        |
| Volts               | 120v                        |
| Watts               | 3.5W                        |

**PHYSICAL**

|           |             |
|-----------|-------------|
| Lamp Base | Medium      |
| Finish    | Clear Amber |
| ANSI Base | E26         |
| Lamp Type | A19         |
| MOD Lamps | 2.36        |
| MOL       | 4.22        |

**ADDITIONAL INFO**

|                            |         |
|----------------------------|---------|
| Warranty                   | 2-Years |
| Rated For Enclosed Fixture | Yes     |

**PACKAGING**

|                |                |
|----------------|----------------|
| UPC            | 045923142260   |
| Case Cube      | 0.6422         |
| Case Height    | 5.71           |
| Case Length    | 16.9           |
| Case Quantity  | 24             |
| Case UPC       | 10045923142267 |
| Case Weight    | 4.13           |
| Case Width     | 11.5           |
| EA Cube        | 0.0185         |
| EA Height      | 4.79           |
| EA Length      | 2.58           |
| EA Quantity    | 1              |
| EA Weight      | 0.12           |
| EA Width       | 2.58           |
| Inner Cube     | 0.1408         |
| Inner Height   | 5.4            |
| Inner Length   | 8.16           |
| Inner Quantity | 6              |
| Inner UPC      | 20045923142264 |
| Inner Weight   | 0.89           |
| Inner Width    | 5.52           |
| Pack Type      | Color Box      |
| Web Length     | 4.22           |
| Web Width      | 2.36           |

**COMPLIANCE**

|                 |                 |
|-----------------|-----------------|
| CA Prop 65      | Lead            |
| Dark Sky Rated  | No              |
| FCC Compliant   | Yes             |
| Location Rating | Wet             |
| NSF Approved    | No              |
| ROHS Compliant  | Yes             |
| Safety Listing  | cULus           |
| California Ban  | Lawful for sale |
| Title 20        | Exempt          |
| T24 Compliant   | No              |