

ROAN

PTL1931-PBR

Like a tree trunk reaching for the sky, Roan is statuesque and statement-making. Each lamp features a cylindrical base wrapped in bleached jute rope, showcasing the beauty of the fiber's weave. An off-white linen drum shade lends a softness to the design, accented by Patina Brass hardware. Available as a table and floor lamp, Roan brings a touch of nature indoors.

*Due to the one-of-a-kind nature of the medium, exact colors and patterns may vary slightly from the image shown.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 31"

Width/Diameter: 22"

Canopy/Backplate: 10"

Product Weight: 23lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Textile

Shade 1 Finish: Off White Linen

Shade 1 Top Width: 21"

Shade 1 Bottom L/W: 0" / 22"

Shade 1 Height: 12"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Wire Length: 96"

Cord Type: SPT-2 BLACK FABRIC

Switch Type: ON/OFF SWITCH ON SOCKET

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 24" x 24" x 28"

Carton 1 Weight: 35lb

Shipping Method: Ground

Country of Origin: VN

