

HOM270CP

Mini circuit breaker, Homeline, 70A, 2 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL



Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	70 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	2P
Short Circuit Current Rating	10 kA
Number of Spaces	2
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	AWG 8...AWG 2 aluminium/copper)1
Type of Packing	Consumer packaging

Complementary

Tightening torque	40.71 lbf.in (4.6 N.m) (AWG 8...AWG 2)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature for Operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	01347-HOM 2 POLE BULK 70-200AMP
Discount Schedule	CPH
GTIN	047569062810
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.00 in (7.62 cm)
Package 1 Width	1.90 in (4.826 cm)
Package 1 Length	3.10 in (7.874 cm)
Package 1 Weight	11.22 oz (318.0 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	1800
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Package 2 Weight	1342.00 lb(US) (608.72 kg)
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Height	3.20 in (8.128 cm)
Package 3 Width	1.90 in (4.826 cm)
Package 3 Length	10.10 in (25.654 cm)
Package 3 Weight	3.64 lb(US) (1.651 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile