

SEABROOK

CB1610-HB

FINISHES

HISTORIC BRONZE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 10"

Width/Diameter: 11.25"

Canopy/Backplate: 6.25"

Product Weight: 5.51lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Opal Matte

Shade 1 Top Width: 11.25"

Shade 1 Height: 7.25"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E26 Medium Base

Bulb Type: A19

Max Wattage: 15

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 15" x 15" x 14"

Carton 1 Weight: 10lb

Shipping Method: Ground

Country of Origin: VN

