Brink | E41512-WT

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Brink brings quiet architectural drama to outdoor lighting through a clean rectangular form and a softly illuminated recessed channel. Finished in Matte Black or White, the design conceals its LED source within a horizontal reveal, allowing light to wash gently across the surface with subtle depth and control. Offered as both a wall sconce and coordinating step light, Brink creates a cohesive exterior lighting story for entries, pathways, stairs, and modern outdoor spaces. Minimal, durable, and refined, it turns a simple line of light into a striking design detail.



MEASUREMENTS

DIMENSION	: 6" W x 8" H x 1.5" Ext
BACK PLATE	: 6" W x 8" H x 4" HCO
HANGING WEIGHT	: 1.45 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,000 Rated (30 Del.)
BULB	: 1 x 10W LED DC Integrated , 10W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Down

FINISHES OPTION

- Architectural Bronze (ABZ)
- Black (BK)
- White (WT)

MATERIAL

Aluminum, Glass

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com