



FF712W



43.5" x 19.13" x 22.5" (H x W x D)

ENERGY STAR certified 19" wide 4.3 cu.ft. top-mount frost-free refrigerator-freezer in a classic white finish

Highlights:

- 19" wide top-mount refrigerator-freezer with a spacious interior to add true convenience to any kitchen space
- ENERGY STAR certified for guaranteed savings and a greener performance
- Compact fit with a top-mount design to ensure full storage convenience

Product Features:

19" Wide Top-Mount Refrigerator-Freezer	Compact 4.3 cu.ft refrigerator-freezer with a spacious interior to add true convenience to any kitchen space
ADA compliant	43 inch height makes both the refrigerator and freezer accessible under ADA guidelines
ENERGY STAR certified	Rated by the DOE to perform with more efficiency than federal standards require, saving your unit energy and you on higher utility costs
Frost-free operation	No-frost convenience for reduced user maintenance
Reversible doors	User-reversible door swing for added flexibility to best accommodate your setting
Compact design	Unique dimensions offers a full 4.3 cu.ft. capacity and 2-door design in a conveniently slim fit
Adjustable glass shelves	Spill-proof shelving for easy cleanup and flexible storage
Door storage	Store tall bottles and condiments right on the door for convenient access
Clear crisper	Get the longest life and best taste out of produce by storing greens in a convenient slide drawer



FF712W Specifications:

Overview	
Height of Cabinet	43.0" (109 cm)
Height to Hinge Cap	43.5" (110 cm)
Width	19.13" (49 cm)
Width with Door Open	20.38" (52 cm)
Depth	22.5" (57 cm)
Depth with door at 90°	39.38" (100 cm)
Capacity	4.3 cu.ft. (122 L)
Defrost Type	Frost-Free
Door	White
Cabinet	White
US Electrical Safety	CSA
Canadian Electrical Safety	CSA-C
Energy Usage/Year	359.0kWh/year
Amps	1.5
Plug Type	NEMA 5-15P
Voltage/Frequency	115 V AC/60 Hz
Weight	78.0 lbs. (35 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101156996
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Interior Light	Yes
Refrigerator - Interior Height	25.0" (64 cm)
Refrigerator - Interior Width	15.0" (38 cm)
Refrigerator - Interior Depth	17.25" (44 cm)
Refrigerator - Shelf Type	Glass
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	10.25" (26 cm)

Freezer - Interior Width	13.0" (33 cm)
Freezer - Interior Depth	12.75" (32 cm)
Freezer - Shelf Type	Glass
Freezer - Shelf Qty	1
Freezer - Full Door Shelves	1
Thermostat Type	Dial
Fan Type	Interior
Refrigerant Type	R600a
Refrigerant Amount	1.02 oz.
High Side PSI	300.0
Low Side PSI	120.0
Compressor Step Height	8.0" (20 cm)
Compressor Step Width	15.0" (38 cm)
Compressor Step Depth	5.5" (14 cm)

