



Technical Data

Color	Black
Sizes Available	7-11
Polymer	Butyl
Thickness	20 Mil
Lining	Unlined
Length	14"
Cuff	Rolled
Grip	Rough
Construction	Unsupported, ESD Safe
Case Dimensions (in)	22.83 x 14.96 x 7.48
Case Weight (lbs)	0.00
Packed	48 Pair/Case
Packaging	Bagged Pair
Certifications	TAA Compliant, EN 16350
Country of Origin	Germany

Performance Data

EN 374	ABIKLNOT
EN 388	201X
EN 374-5	Bacteria, Fungi and Virus

Assurance®

20 Mil Butyl Rubber Glove with Rough Grip-14"

- 20 Mil Bromine Butyl Rubber ideal for full hand chemical emersion
- The addition of bromine enhances temperature resistance, offering superior durability
- Designed to handle extreme exposure to exposure to polar organic compounds such as ketones, carboxylic acids, esters, and amine derivatives
- 14 " length for extended forearm protection
- Rough finish to maintain better grip
- Tested to EN 16350 for electrostatic properties to help protect any static sensitive materials or equipment

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
BUT05R/7	Black	7	616314948329	10616314948326	20616314948323
BUT05R/8	Black	8	616314948404	10616314948401	20616314948408
BUT05R/9	Black	9	616314948442	10616314948449	20616314948446
BUT05R/10	Black	10	616314948480	10616314948487	20616314948484
BUT05R/11	Black	11	616314948527	10616314948524	20616314948521