



FF63BKADA



32.38" x 23.63" x 23" (H x W x D)

24" wide residential ENERGY STAR certified 5.8 cu.ft. ADA height all-refrigerator made in Europe with automatic defrost operation in a black finish

Highlights:

- 32" height for use under lower ADA compliant counters
- Automatic defrost ensures minimum user maintenance
- Deluxe interior with glass shelves, door storage, and a scalloped wine shelf

Product Features:

24" Wide European All-Refrigerator	Freezerless refrigerator designed and manufactured in Europe for residential use under the counter
Peak24 Series	European-made collection for recessed installation featuring large capacity interiors, ENERGY STAR certified performances, and versatile style
ADA compliant	32" height to fit under lower ADA compliant counters
ENERGY STAR certified	Rated by the DOE to perform with more efficiency than federal standards require, saving your unit energy and you on higher utility costs
Slim undercounter dimensions	Ideal 24" footprint offers full 5.8 cu.ft. storage capacity in a slim fit
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Automatic defrost	Reduced maintenance with auto defrost system
Adjustable glass shelves	Rearrange the refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Door shelves	Store tall bottles and condiments right on the door for convenient access



FF63BKADA Specifications:

Overview	
Nominal Height	32.0" (81 cm)
Height of Cabinet	32.0" (81 cm)
Height to Hinge Cap	32.38" (82 cm)
Nominal Width	24.0" (61 cm)
Width	23.63" (60 cm)
Nominal Depth	23.0" (58 cm)
Depth	23.0" (58 cm)
Depth with Handle	24.63" (63 cm)
Depth with door at 90°	45.38" (115 cm)
Capacity	5.8 cu.ft. (164 L)
Defrost Type	Automatic
Door	Black
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	280.0kWh/year
Amps	1.4
Weight	100.0 lbs. (45 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101069166
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Wine Bottle Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R600a
Refrigerant Amount	0.64oz.
High Side PSI	180.0
Low Side PSI	80.0

Interior Light	Yes
Dimensions	
Interior Height	26.25" (67 cm)
Interior Width	21.0" (53 cm)
Interior Depth	18.0" (46 cm)
Compressor Step Height	5.5" (14 cm)
Compressor Step Width	21.0" (53 cm)
Compressor Step Depth	6.0" (15 cm)

