

Garant**Micro-boring head Ø 0.3 - 7.1 mm:****Order data**

Order number	237490
GTIN	4045197681409
Item class	29W

Description**Version:****Adjustment accuracy 0.01 mm per graduation / with vernier 0.002 mm on the Ø.****Application:**

With cutting insert No. 237621, adapter No. 237624 and insert No. 237625.

Technical description

Reach L ₁	25 mm
External Ø D ₁	25 mm
Shank Ø D ₂	10 mm
Ø D ₃	4 mm
Through-coolant	yes
Type of product	Boring tool