

BECKHAM

B6340-TBZ

Designed for the exteriors of large-scale homes, the Beckham sconce takes the form of a classic box lantern with a modern, elongated silhouette. Within the frame, two or four cream candles emit ambient light in all directions. Available in either a Forged Iron or Textured Bronze finish, Beckham blends sleek geometry with old-world charm.

FINISHES

TEXTURED BRONZE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 40"

Width/Diameter: 11.75"

Canopy/Backplate: 11.75"

Product Weight: 28.16lb

Extension: 13"

Top to Center: 21.5"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade

Shade 1: Glass

Shade 1 Finish: Clear

Shade 1 Top Width: 11.5"

Shade 1 Height: 32.25"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 4

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"):

No

Dark Sky: No

SHIPPING

Carton 1: 44" x 17" x 17"

Carton 1 Weight: 39lb

Shipping Method: Ground

Country of Origin: CN

