



TEGERA® 913

Learn more

FOOD APPROVED, CUT RESISTANT GLOVE

This blue coloured cut resistant glove (level C) has extended knitted cuff for extra protection of the wrist. Perfect for handling food stuffs. A great combination of soft comfort and cut protection thanks to 13 gg knitted with the CRF® cut resistant Technology. Each pair individually packed.

CHARACTERISTICS

- Good fingertip sensitivity
- Flexible
- Comfortable
- Breathable

FUNCTIONS

- Approved for handling foodstuffs
- Extra long
- Soft

CRF®

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments

PRIMARY AREAS OF USE

Fishing industry work, Food handling, Hotel- and restaurant work, Kitchen work

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Food and beverage processing

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cut resistant gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 13
LINING MATERIAL CRF® Technology, Glass fibre thread, HPPE, Polyester, Spandex
LENGTH 265-310 mm
DEXTERITY 5
COLOUR Blue
PAIRS PER: BUNDLE/CARTON 12/60
DISPLAY TYPE Bag with euro slot
CUFF STYLE Extended knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level C
CUT RESISTANCE (EN ISO 13997) TDM: 12.9 N
OUTER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Polyester, Glass fibre thread, Natural latex, Elastane

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC
EN 388:2016+A1:2018 3X4XC

ANSI A3 CUT

ANSI 3 ABR

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
6	XS	913-6	7340118322841
7	S	913-7	7340118322858
8	M	913-8	7340118322865
9	L	913-9	7340118322872
10	XL	913-10	7340118322827
11	XXL	913-11	7340118322834

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.