

Palm-dipped with PU and highly breathable.

TEGERA® 878

Learn more

OUR THINNEST ESD GLOVE

Our thinnest ESD glove, palm-dipped with PU for maximum usability and comfort. For ESD-protected work areas where maximum dexterity and fingertip sensitivity is needed. Thin 18 gg fibre and highly breathable to ensure all-day comfort.

CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Good grip
- Extra comfortable

FUNCTIONS

- ESD
- Conforms with IEC 61340-5-1 (ESD)
- Ultra thin
- Super soft

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF
Scratches, lacerations, Drying out

PRIMARY ENVIRONMENTS OF USE
Dry environments, Clean environments

PRIMARY AREAS OF USE
Electronics work, Fine assembly

PRIMARY INDUSTRIES OF USE
Automotive manufacturing, Automotive repair and maintenance, Electrical equipment manufacturing, Electricity and gas supply, Electronics manufacturing, Facility management services, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Transport equipment manufacturing

TYPE OF WORK
Light weight

SPECIFICATION
TYPE ESD gloves, Precision work gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 18
LINING MATERIAL Nylon
LENGTH 205-270 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR White
PAIRS PER: BUNDLE/CARTON 6/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL PU
CUFF STYLE Rolled edges
CUFF MATERIAL Textile
INNER MATERIAL SPECIFICATION Nylon
OUTER MATERIAL SPECIFICATION Polyurethane

COMPLIANCE
CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 1020X

IEC 61340-5-1:2016 R < 1.0 x 10⁹ Ω

ANSI 3 ABR

Do not wash

SIZE		ARTICLE NUMBER	EAN
5	XXS	878-5	7340118398532
6	XS	878-6	7340118398624
7	S	878-7	7340118398716
8	M	878-8	7340118398808
9	L	878-9	7340118398891
10	XL	878-10	7340118398983
11	XXL	878-11	7340118399072
12	3XL	878-12	7340118399164

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.