Hover | E21370-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Minimalist batons of extruded Black aluminum are fitted with V shaped acrylic diffusers for a wider beam of light. They can be arranged in numerous configurations allowing creativity and design of your own unique sculpture.



MEASUREMENTS

DIMENSION	: 60" L x 1.5" W x 1.5" H
MAX OAH	: 123.5" OAH
CANOPY	: 5.5" W x 1.5" H x 16.5" L
HANGING WEIGHT	: 4 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,500 Rated (2,000 Del.)
BULB	: 1 x 26W LED DC Integrated , 26W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1 Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

MATERIAL

Aluminum, Acrylic

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com