

# Specialty Recessed



**P6917-TG**

**COMPLETE ROUND**

Unwired unit: White trim, housing, plaster frame, clips and 4-1/2 feet of wire. All are UL listed for damp locations. Therma-Gard™ automatic resetting thermal protection.

Cat. No.	<b>P6917-TG</b>
Desc.	Open trim, unwired
Finish	White
Plaster Frame	6-5/8" sq.
Recess Depth	5-3/4"
Ceiling Opening	4-1/2"
Trim O.D.	5-7/8"
Lamp	45w BR30, 50w PAR30




**P6952-16TG**

**BATH HEATER LIGHT**

Complete with housing, trim and 26" adjustable bar hangers. Therma-Gard™ automatic resetting thermal protection. Junction box has riveted ground, 9 K.O.'s. UL listed for damp locations. Thru-branch wiring, 4 in, 4 out.

Cat. No.	<b>P6952-16TG</b>
Desc.	Heater light
Finish	Satin aluminum
Plaster Frame	8-3/8" x 13"
Recess Depth	7-3/4"
Ceiling Opening	6-7/8"
Trim O.D.	7-3/4"
Lamp	250w R 40



**P6414-30TG , P6416-30TG**


**COMPLETE SQUARE**

Complete with housing and trim. Flat white glass. Torsion springs for easy relamping. UL listed for damp locations. Therma-Gard™ automatic resetting thermal protection.

Cat. No.	<b>P6414-30TG</b>	<b>P6416-30TG</b>
Desc.	Pre-wired	White
Finish	Pre-wired	White
Recess Depth	4-1/4"	4-1/4"
Ceiling Opening	8-1/8"	10-1/8"
Trim (Sq.)	9-1/2"	11-1/2"
Lamp	100w	150w

## Installation Hardware for P6917, P6414 and P6416

**P8700-01** Four clips for finished or suspended ceiling installation.



P8700-01

**P8716-01** Accessory bar hangers for new construction. For use with complete squares (P6914, P6416) and complete rounds (P6917).



P8716-01