Penrose | E21261-BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A cubist work of art, the Penrose collection carefully calculates the structural form of a cube space when corners do not meet. This tracery of this shape is emphasized by its dedicated LED light source housed within aluminum channels and then cast in various directions. Available in Matte Black or Gold, this series is a feat of human engineering in design. Translating a mathematical challenge into a sculptural work of art with the function of delivering light to interior spaces.



*max overall height

MEASUREMENTS

DIMENSION	: 7" L x 7" W x 18" H
MAX OAH	: 140" OAH
CANOPY	: 5.5" W x 1.5" H x 8" L
HANGING WEIGHT	: 5.7 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,840 Rated (630 Del.)
BULB	: 1 x 23W LED PCB Integrated , 23W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac CL
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)
Gold (GLD)

MATERIAL

Aluminum, Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com