



jalas® ZENIT EVO 7100

ASTM F2413-18 M/I/C/SD 35 EN ISO 20345:2022+A1:2024 S1,SR,FO,SC

Learn more

GIVES YOU THE POWER TO MOVE

A light, soft, comfortable safety shoe with quality protection and outstanding ergonomics. The knitted textile upper with padded Memory foam supports and protects your feet in light duty work. An oil resistant RPU outer sole gives excellent grip, and JALAS® aluminium toe cap protection and double impact protection zones in PORON® XRD® keeps feet safe.

CHARACTERISTICS

- Excellent grip
- Perfect fit
- Extra comfortable
- Very breathable
- Excellent shock absorption
- Extremely light

FUNCTIONS

- Low weight
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Padded shaft edge in memory foam
- Ventilating insole
- Ergonomically shaped
- Soft
- Conforms with IEC 61340-5-1 (ESD)
- Free from animal-derived materials

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Antistatic, Slipping

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, Dry environments, Clean environments

SPECIFICATION

TYPE Safety footwear, Low shoes
CATEGORY Cat. II
FITTING Regular
COLLECTION Zenit Evo
UPPER MATERIAL Knitted textile
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester
INSOLE JALAS 8303 FX3 Supreme
INNERSOLE MATERIAL Textile, Soft EVA, Rigid EVA, Polyester-based conductive thread, Neo foam, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL RPU outsole
FASTENING Laces
COLOUR Black
NET WEIGHT, (SIZE 42) 1.05 kg

COMPLIANCE

CE Cat. II

ASTM F2413-18
M/I/C/SD 35

EAC

EN ISO
20345:2022+A1:2024
S1,SR,FO,SC

TP TC 019:2011

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	7100-35	6408487507632
36	3	4	5	7100-36	6408487507649
37	4	5	6	7100-37	6408487507656
38	5	5.5	6.5	7100-38	6408487507663
39	6	6.5	7.5	7100-39	6408487507670
40	6.5	7.5	8.5	7100-40	6408487507687
41	7	8	9	7100-41	6408487507694
42	8	9	10	7100-42	6408487507700
43	9	9.5	11	7100-43	6408487507717
44	10	10.5	11.5	7100-44	6408487507724
45	10.5	11	12.5	7100-45	6408487507731
46	11	12	13	7100-46	6408487507748
47	12	13	14	7100-47	6408487507755
48	13	13.5	14.5	7100-48	6408487507762

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.