
Latitude | E23422-SN

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Soft oval forms offer a modern and playful touch to this LED wall mounted sconce. The face of the fixture is a light guided White acrylic diffuser that even illuminates the edge-lit LED light source. The sleek shape is made even more attractive by the bright illumination provided by the fixture itself. Great for use in bathrooms or corridors, the fixture is ADA compliant and available in 4 lengths. A recessed housing behind the fixture not only mounts the fixture with an attractive extension that makes it appear to be floating off the wall, but it also features a 5-step color temperature select switch allowing you to discreetly adjust the LED lighting to 5 settings ranging from a warmer 2700K to 3000-3500-4000 and daylight white 5000K. These additional product features thereby give more latitude to the design applications without special requests.



MEASUREMENTS

DIMENSION	: 24" W x 5" H x 2.5" Ext
BACK PLATE	: 4" W x 13.5" H x 12" HCO
HANGING WEIGHT	: 3.96 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 2,000 Rated (1,350 Del.)
BULB	: 1 x 20W LED AC Intergrated , 20W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: Backlit

FINISHES OPTION

- Black (BK)
- Gold (GLD)
- Polished Chrome (PC)
- Satin Nickel (SN)

MATERIAL

Aluminum, Polycarbonate

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Horizontal/Vert
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com