



Project / Job Name: \_\_\_\_\_

Location: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Notes: \_\_\_\_\_

**65-944** - 45/60/80 Watt; 3K/4K/5K CCT Selectable LED Large Adjustable Wall Pack; 120-277 Volt; Bronze Finish



### GENERAL

Company	NUVO
EA Height	5.51
EA Width	9.65
EA Length	12.2
Bulb Included	Integrated
Dimmable Text	0-10V Dimming
Extends (in)	11.04
Material	Die-cast Aluminum
Fixture Type	Wall Pack
Status	Active
Style	Utility
Surge Protection	Built-in surge protection - 4KV
Total Harmonic Distortion	9.81%
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	Bronze
Amps	0.375-0.162/0.500-0.217/0.667-0.289A
Integrated Features	Integrated Photocell
IOT Enabled	No
Lens Finish	Opaque
Lens Material	Impact Resistant PC
Lensed	Yes
Photo Cell	Yes - Bypassable
Power Factor	>0.9
Indoor Outdoor	Outdoor
Product Technology	LED

### ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	65x95
Color Temp	Soft White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-40C (-40F) to +40C (+104F)
HID Equivalent	100W-250W
Lumens	6251L-11264L
Volts	120V-277V
Watts	45W/60W/80W

### PHYSICAL

Lamp Base	Integrated
Finish	BRONZE
ANSI Base	Integrated
Lamp Type	Integrated LED

### ADDITIONAL INFO

Warranty	5-Years
----------	---------

### PACKAGING

UPC	045923410307
Case Cube	1.8599
Case Height	12.2
Case Length	20.28
Case Quantity	4
Case UPC	10045923410304
Case Weight	25.9
Case Width	12.99
EA Cube	0.3754
EA Height	5.51
EA Length	12.2
EA Quantity	1
EA Weight	5.95
EA Width	9.65
Pack Type	Box
Web Height	4.41
Web Width	8.5

### COMPLIANCE

CA Prop 65	Lead
DLC ID	S-BZVW67
FCC Compliant	Yes
IP Rating	IP65
Location Rating	Wet
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24 Compliant	No