

HUNTLY

PTL3727-BRZ/CIB

FINISHES

BRONZE w/ Ceramic Ivory Breakstone
Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 26.5"
Width/Diameter: 20"
Length: 15"
Canopy/Backplate: 5"
Product Weight: 12.1lb
Canopy/Backplate Shape: Oval
Sloped Ceiling Compatible: No
Living Finish: No
Uplight Only: No

Shade

Shade 1: Fabric
Shade 1 Finish: Natural Linen
Shade 1 Top Length: 14.25"
Shade 1 Top Width: 19.25"
Shade 1 Bottom L/W: 15" / 20"
Shade 1 Height: 10"

ELECTRICAL



Bulb 1

Bulb Included: No
Socket: E26 Medium Base
Bulb Type: A19
Max Wattage: 15
Bulb Quantity: 1
Bulb Included: No
Cord Type: SPT-2 BROWN FABRIC
Switch Type: ON/OFF SWITCH ON SOCKET
Gem Box Required (2"x3"): No
Dark Sky: No

SHIPPING

Carton 1: 24" x 20" x 27"
Carton 1 Weight: 24lb
Shipping Method: Ground
Country of Origin: PH

