






PRODUCT DESCRIPTION

Shallow glass domes encase edge-lit LED panels, creating a captivating play of light that highlights the void within each fixture while delivering evenly distributed illumination both upwards and downwards where applicable. A meticulously crafted frame conceals the hardware, resulting in a sleek, modern LED composition. The collection is available in two sophisticated finishes - Clear Glass with a Gold-plated frame and Mirror Smoked Glass with a Gunmetal frame - and includes a 2-light LED pendant, a versatile flush mount that doubles as a wall-mountable fixture, and a portable lamp option.



MEASUREMENTS

DIMENSION	: 12" L x 12" W x 4.25" H
CANOPY	: 11" W x 1" H x 11" L
HANGING WEIGHT	: 3.55 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,640 Rated (780 Del.)
BULB	: 1 x 16W LED AC Integrated , 16W Total
BULB INCLUDED	: (Integrated)
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Gunmetal (GM)

Natural Aged Brass (NAB)

GLASS

Smoke 138

MATERIAL

Steel, PC

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com