



Fibre-Metal® Roughneck™ P2

Type I, Non-Vented, Cap-Style Smooth Dome
Hard Hat with High Heat Resistant Proprietary
Fiberglass Shell, 8-Point SuperEight™ Suspension
and Wheel Ratchet Adjustment, Includes Quick-
Lok® Accessory

- High heat Fiberglass-resin compound
- Chip and nick resistant
- Molded-in color
- Smooth matte finish
- High heat resistant up to 500°F (260°C)
- Eight-point suspension

Technical Data

Color	Gray, Red, Green, White, Yellow, Dark Blue, Black, Orange
Sizes Available	OS
Packaging	Bagged Each
Packed	20/Case
Case Dimensions (in)	23.00 x 19.00 x 23.00
Case Weight (lbs)	22.99
Country of Origin	Mexico
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class G

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
P2HNQRW11A000	Black	OS	821812541808		00821812541853
P2HNQRW71A000	Dark Blue	OS	821812533551		00821812533568
P2HNQRW09A000	Gray	OS	821812541785		00821812541839
P2HNQRW74A000	Green	OS	821812533575		00821812533582
P2HNQRW03A000	Orange	OS	821812546001		00821812546018
P2HNQRW15A000	Red	OS	821812541884		00821812541891
P2HNQRW01A000	White	OS	821812378206		00821812378213
P2HNQRW02A000	Yellow	OS	821812378183		00821812378190