



025-4126

Standing Seam Bar Anchor: Nylon-Tipped Screws

FEATURES :

- Easy to install, reusable non-penetrating anchor point
- 360° swivel D-ring connection point for SRLs, energy absorbing lanyards and VLLs
- Accommodates a wide range of standing seams
- For sloped or flat standing seam roofs with minimum gauge 26
- (12) Stainless steel set screws with nylon tips
- 1 user maximum
- Minimum Breaking Strength: 5,000 lbs. (22 kN)
- Dimensions: 8" x 2.25" x 4.5" (20x5.7x11.5 cm)
- Not for use with HLLs or for Material Hauling

ATTACHMENT POINT(S) :

- 1 Swivel D-ring

ITEM WEIGHT :

- 3 lbs (1.4 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-140.6 kg)
OSHA	Up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	N/A
OSHA	1926.502, 1910.140, 1910.66

COMPATIBLE COMPONENTS	
024-4115	Standing Seam Bar Anchor: Steel Screws
025-4127	Standing Seam Nylon-Tipped Set Screws (Set of 12)
025-4128	Standing Seam Steel Set Screws (Set of 12)

COMPONENT	MATERIAL SPECIFICATION
Anchor	Aluminum
D-ring	Stainless steel
Screws	Stainless steel, nylon
Label Cover	Polyester