



Project / Job Name: _____

Location: _____

Fixture Type: _____

Notes: _____

S14228 - 8 Watt A19 LED; 2000K CCT; Medium Base; Clear Glass; Amber Coil Filament; Dimmable; 120 Volt



GENERAL	
Company	SATCO
EA Height	4.79
EA Width	2.58
EA Length	2.58
Dimmable Text	Forward or Reverse Phase; Line Voltage
Lamp Filament	Spiral
Material	Glass
Fixture Type	Miniature
Status	Active
Surge Protection	Built-in surge protection - 2.5KV
Total Harmonic Distortion	<10%
CCT Selectable	No
Wattage Selectable	No
Finish Family	Clear
Amps	0.090A
Lens Material	Glass
Operating Position	Universal
Power Factor	>0.7
SDS Class	LED_Lamp
Indoor Outdoor	Indoor and Outdoor
Product Technology	LED
Incandescent Equivalent	60W

ELECTRICAL	
CCT (Kelvin Temp)	2000K
Dimmable	Yes-Dimmable
Hours Rated	15000
Beam Angle (degree)	300
Color Temp	Warm White
CRI	90+
Dimming Type	Linear Dimming, Phase cut
Operating Frequency	60Hz
Operating Temp	-25C (-13F) to +40C (+104F)
Lumens	800L
Volts	120v
Watts	8W

PHYSICAL	
Lamp Base	Medium
Finish	Clear Amber
ANSI Base	E26
Lamp Type	A19
MOD Lamps	2.36
MOL	4.22

ADDITIONAL INFO	
Warranty	2-Years
Rated For Enclosed Fixture	Yes

PACKAGING	
UPC	045923142284
Case Cube	0.6422
Case Height	5.71
Case Length	16.9
Case Quantity	24
Case UPC	10045923142281
Case Weight	4.13
Case Width	11.5
EA Cube	0.0185
EA Height	4.79
EA Length	2.58
EA Quantity	1
EA Weight	0.12
EA Width	2.58
Inner Cube	0.1408
Inner Height	5.4
Inner Length	8.16
Inner Quantity	6
Inner UPC	20045923142288
Inner Weight	0.89
Inner Width	5.52
Pack Type	Color Box
Web Length	4.22
Web Width	2.36

COMPLIANCE	
CA Prop 65	Lead
Dark Sky Rated	No
FCC Compliant	Yes
Location Rating	Wet
NSF Approved	No
ROHS Compliant	Yes
Safety Listing	cULus
California Ban	Lawful for sale
Title 20	Exempt
T24 Compliant	No