Pilar | E14373-SSN

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

This outdoor collection is cast in concrete for maximum durability in harsh climates such as coastal environments. Available in your choice of a lighter Sandstone or darker Greystone Aggregate, both are powered by dual integrated LED boards for efficient and long-life operation.



MEASUREMENTS

DIMENSION	: 5" L x 5" W x 13" H x 4" Ext
BACK PLATE	: 4" W x 0.67" H x 6.5" HCO
HANGING WEIGHT	: 6.04 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,400 Rated (1,200 Del.)
BULB	: 2 x 7W LED E26 Medium , 7W Total
BULB INCLUDED	: (Included)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Up/Down

FINISHES OPTION

Greystone (GSN)
Sandstone (SSN)

MATERIAL

Concrete, SS, Glass

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 20000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com