

CABLE TIES

UV & Weather Resistant (Black)

Standard - Black Series



SPECIFICATIONS

- cULus Listed for Positioning Devices. UL62275.
- **Temperature Rating:** Min., -40°F to Max., 185°F (-40°C to 85°C)
- **Ideal Storage:** 23°C, Humidity 50%, Avoid storing cable ties next to warm objects.
- **Type 21 AH-2:** "Suitable for use in air-handling spaces (Plenums)".

FEATURES

- Made from weather resistant Nylon 66 for applications exposed to outside elements.
- UV resistant and Black color only.
- Made of high-strength Nylon 66 that resists abrasion and chemicals such as common oils, greases, solvents, dilute acids and alkalines.
- Fungus-resistant, self-extinguishing and have excellent dielectric properties.

CAT. NO.	MAX. WIRE/CABLE SIZE (L)	MAX BUNDLE DIAMETER	TENSILE STRENGTH	LENGTH (IN.)	WIDTH (IN.)	STD. PKG. QTY.	STD. CTN. QTY.
4180	4"	0.800	18 Lbs	4.000	0.095	100	5,000
4180X	4"	0.800	18 Lbs	4.000	0.095	1000	5,000
4500	4"	1.430	50 Lbs	4.750	0.095	100	5,000
4500X	4"	1.375	50 Lbs	4.750	0.100	1000	5,000
5180	5"	1.300	18 Lbs	5.500	0.140	100	3,000
5180X	5"	1.300	18 Lbs	5.500	0.140	1000	3,000
5400	5"	1.320	40 Lbs	6.250	0.181	100	3,000
5400X	5"	1.320	40 Lbs	6.250	0.181	1000	3,000
6500	6"	1.810	40 Lbs	7.500	0.189	100	3,000
7500	7"	2.060	50 Lbs	8.000	0.095	100	3,000
7500X	7"	2.060	50 Lbs	8.000	0.095	1000	3,000
8180	8"	2.060	18 Lbs	8.000	0.140	100	3,000
8180X	8"	2.060	18 Lbs	8.000	0.140	1000	3,000
8400	8"	1.940	40 Lbs	8.000	0.189	100	3,000
8400X	8"	1.940	40 Lbs	8.000	0.189	1000	3,000
8500	8"	2.000	50 Lbs	8.000	0.300	100	2,000
8500X	8"	2.000	50 Lbs	8.000	0.300	1000	2,000
8750	8"	2.000	75 Lbs	8.000	0.300	100	2,000
81200	8"	3.300	120 Lbs	8.000	0.140	100	2,000