

PHILIPS

Home Access

Electronic deadbolt

1100 series

Philips Fingerprint Keypad Electronic Deadbolt

DDL0M1011X-1H

Effortless entry classic look with 3 ways to unlock



Specifications

Overview

| | |
|--------------|----------------------|
| Material | Aluminum alloy |
| Color | Nickel / Matte black |
| Bolt type | Dead bolt |
| Keyway | SC1 |
| Connectivity | N/A |

Unlock Methods

| | |
|------------------------|------------------------------|
| Unlocking from outside | Fingerprint / PIN code / Key |
| Unlocking from inside | Thumb turn |

Max Credentials Capacity

| | |
|-----------------|-----|
| Fingerprint | 50 |
| Master PIN code | 1 |
| User PIN code | 100 |
| Traditional key | 2 |

Modes

| | |
|----------------|-----------|
| Operation mode | Auto mode |
| Security mode | Away mode |

Power

| | |
|--------------|------------------------------------|
| Power supply | 4 1.5V AA (LR6) alkaline batteries |
|--------------|------------------------------------|

Operating Environment

| | |
|-------------|--------------------|
| Temperature | From -35 C to 66 C |
| Humidity | 0-95% |

Installation Requirements

| | |
|-------------------|--|
| Door thickness | 1-3/8 to 2 inch (35-50mm) |
| Opening direction | Left inside / Left outside Right inside / Right outside |
| Cross bore hole | 1-1/2 or 2-1/8 inch (38/54mm) |
| Backset | 2-3/8 or 2-3/4 inch (60mm/70mm) |

Key Features

| | |
|--------|---|
| Safety | Meets ANSI/BHMA standard AES128 Local storage |
| Alarms | Low battery alarm Wrong entry limit alarm Jam alarm |



Fingerprint
unlock



PIN code
unlock



Traditional
key



Ultra-long
battery life



2 years
warranty