

High quality leather glove with superior comfort, flexibility, and Kevlar® seams.

TEGERA® WELDING 126A

Learn more

SUPERIOR PRECISION FOR WELDING

High quality leather glove with superior comfort, flexibility, and Kevlar® seams for extra durability. Long cuff provides extra protection against molten splash. Elasticated wrist for better fit, unlined for extra tactility and precision.

CHARACTERISTICS

- High level of protection
- Extremely good fingertip sensitivity
- Extra flexible
- Durable
- Perfect fit

FUNCTIONS

- Withstands contact heat up to 100°C
- Heat-resistant sewing thread
- Reinforced index finger
- KEVLAR® thread in the seams which resists 427° C short-term heat exposure (max operating limit) and 204° C longer-term heat exposure (constant operating limit)

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Burn injuries, Heat injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

Warm environments, Dirty environments, Harsh environments

PRIMARY AREAS OF USE

Assembly, Engineering, Forest work, Foundry, Gardening, Glass industry work, Hot work, Installation work, Marine work, Metalwork, Mining, Paper industry work, Repair work, Welding, Wood industry work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Glass, ceramics and construction materials, Metal manufacturing and fabrication, Transport equipment manufacturing, Agriculture, forestry and fishing, Facility management services, Oil and gas extraction, Rubber and plastics manufacturing, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Transportation and logistics, Building and construction, Mining and quarrying, Warehousing, Pulp and paper, Public safety, security and defence, Retail and wholesale

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Heat protection gloves, Welding gloves
CATEGORY Cat. II
COLLECTION Welding
PALM MATERIAL Full grain goatskin of top quality
BACK MATERIAL Full grain goatskin of top quality
LINING Unlined
LENGTH 310-350 mm
DEXTERITY 5
COLOUR White
PAIRS PER: BUNDLE/CARTON 12/60
DISPLAY TYPE Thread
FASTENING Elasticated 180°
CUFF STYLE Safety cuff
CUFF MATERIAL Leather
OUTER MATERIAL SPECIFICATION Leather

COMPLIANCE

CE Cat. II
EAC TP TC 019:2011
EN ISO 21420:2020
EN 388:2016+A1:2018 2111X
EN 407:2020 412X4X
EN 12477:2001+A1:2005 Type B
EN 1149-2:1997
EN 659:2003+A1:2008
ANSI 3 ABR

Warning, this model is not intended for use in wet conditions

SIZE		ARTICLE NUMBER	EAN
7	S	126A-7	7340118312293
8	M	126A-8	7340118312316
9	L	126A-9	7340118312330
10	XL	126A-10	7340118312255
11	XXL	126A-11	7340118312279

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.