



Fibre-Metal® Roughneck™ P2

Type I, Non-Vented, Cap-Style Smooth Dome
Hard Hat with Heat Resistant Fiberglass Shell, 8-
Point SuperEight™ Suspension and Wheel
Ratchet Adjustment

- Fiberglass-resin compound
- Chip and nick resistant
- Molded-in color
- Smooth matte finish
- Heat resistant up to 370°F (188°C)
- Eight-point suspension

Technical Data

Color	Green, Gray, Yellow, Dark Blue, Orange, White, Black, Red
Sizes Available	OS
Packaging	Bagged Each
Packed	20/Case
Case Dimensions (in)	23.00 x 19.00 x 23.00
Case Weight (lbs)	22.99
Country of Origin	Mexico
Shell Material	Fiberglass Composite
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Certifications	ANSI/ISEA Z89.1, CSA Z94.1 Certified, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class G

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
P2ARW11A000	Black	OS	883940088563		00883940088570
P2ARW71A000	Dark Blue	OS	883940088648		00883940088655
P2ARW09A000	Gray	OS	883940088549		00883940088556
P2ARW74A000	Green	OS	883940088662		00883940088679
P2ARW46A000	Orange	OS	883940088624		00883940088631
P2ARW15A000	Red	OS	883940088600		00883940088617
P2ARW01A000	White	OS	883940088501		00883940088518
P2ARW02A000	Yellow	OS	883940088525		00883940088532