



LED CFL RETROFIT

Tunable Wattage & CCT



PRODUCT FEATURES

- **TUNABLE CCT (2700K/3500K/4000K/5000K)**
- **TUNABLE POWER (8W/10W/12W/15W)**
- Plug & Play Mode - Type A
- Retrofit / Bypass Mode - Type B
- Frosted Lens
- 0-10V Dimming Available
- 120-277 Voltage Rating, PF > 0.9
- CRI > 80
- G24Q (4-Pin) Base
- NSF Certified
- UL Certified
- 35,000 Hour Lifetime Rating
- 5-Year Limited Warranty
- Operating Temperature Range: -4°F to 113°F (-20°C to 45°C)

PRODUCT SPECIFICATIONS

MODEL	ITEM #	POWER (W)	LUMENS (LM)	CCT (K)	LENGTH (IN)	EFFICIENCY (Lm/W)	BEAM ANGLE
CL97-8.15WCFABSRMF-00K	L15PLTCABL97	8	970	2700	6.69	122	220°
		10	1220	3500			
		12	1460	4000			
		15	1800	5000			

