


PRODUCT DESCRIPTION

Low voltage garden lights consisting of classic shaped shades to brighten your outdoor space. Choose from various lighting elements that pair with matching poles. In-ground stakes or bolt down installation mounting options are provided. Extension rods in 8-inch increments sold separately.



MEASUREMENTS

DIMENSION	: 6.75" W x 6.75" H x 1.25" Ext
MAX OAH	: 4.5" W x 4.5" H
HANGING WEIGHT	: 1.32 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,400 Rated (880 Del.)
BULB	: 1 x 14W LED DC Integrated , 14W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

- Architectural Bronze (ABZ)
- Black (BK)
- Satin Aluminum (SA)

MATERIAL

Aluminum

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 25000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com