



Monoprice™

4K Certified High-Speed Slim HDMI® Cable – 4K60Hz, 18Gbps, HDR, CL2 Rated, Gold-Plated, Black

Next-Level Ultra HD Connectivity for Stunning Visuals and Smooth Motion

Deliver crystal-clear visuals and immersive audio with the Monoprice™ 4K Certified High-Speed Slim HDMI® Cable. Engineered for seamless connectivity, this slim-profile cable supports 4K resolution at 60Hz, 18Gbps bandwidth, and HDR, providing lifelike colors, sharp contrast, and smooth motion. The CL2-rated jacket makes it safe for in-wall installations, while gold-plated connectors ensure a reliable, corrosion-resistant connection. Whether streaming, gaming, or connecting home theater components, this cable delivers consistent, high-performance transmission for an uncompromising entertainment experience.

Lengths: 3, 4, and 6 feet

- 4K certified high-speed performance guarantees support for 4K@60Hz with 18Gbps bandwidth, delivering crisp detail, vivid color, and smooth motion
- HDR compatibility provides lifelike contrast and an expanded color range for a more immersive viewing experience
- Slim, flexible design offers a streamlined profile that makes routing behind TVs and components easier without sacrificing durability
- CL2 rated for in-wall installations meets safety requirements for residential in-wall use, allowing for clean and professional setups
- Gold-plated connectors ensure optimal signal transfer and corrosion resistance for long-term reliability
- Audio Return Channel (ARC) support simplifies audio connections by sending sound directly from your TV to your receiver or soundbar
- Universal HDMI® compatibility works seamlessly with TVs, monitors, projectors, gaming consoles, streaming devices, and more
- Monoprice quality assurance is backed by rigorous testing and lifetime support for peace of mind and lasting performance



IMMERSIVE, TRUE-TO-LIFE VISUALS

Experience stunning 4K60Hz resolution with HDR support, delivering vibrant colors, deep contrast, and smooth motion for movies, gaming, and streaming.



EFFORTLESS INSTALLATION IN ANY SPACE

The slim, flexible cable design easily routes through tight spaces or behind equipment without tangling, making setup clean and hassle-free.



PROFESSIONAL-GRADE SAFETY FOR IN-WALL USE

CL2-rated construction meets residential in-wall code requirements, ensuring both a polished look and safety compliance for permanent installations.

Full Specs

P/N	47916, 47917, 47918
Cable Type	Certified High-Speed HDMI Cable
HDMI Version	HDMI 2.0
Bandwidth	Up to 18 Gbps
Resolution Support	Up to 4K @ 60Hz
HDR Support	HDR, HDR10, Deep Color
Audio Support	Dolby TrueHD®, DTS-HD Master Audio®
Connector Type	HDMI Type A (Standard)
Connector Plating	Gold-Plated
Connector Shell Material	Aluminum Alloy
Cable Jacket Material	Black PVC
Shielding	Triple Shielded
Compliance	HDMI LA Certified, RoHS Compliant
Additional Features	Slim Profile for Tight Spaces
Available Lengths	3 ft (47916), 4 ft (47917), 6 ft (47918)
Color	Black