



Technical Data



Bouton® Optical Commander™ Semi-Rimless Safety Glasses with Gloss Black Frame, Clear Lens and Anti-Scratch / Anti-Fog Coating

- Lightweight, semi-rimless design offers extensive eye coverage and all day comfort
- Bayonet style temples with non-slip rubber pads provide a secure fit
- Adjustable rubber nose pads offer a custom, comfortable fit
- 9.5 Base curve lens
- Meets ANSI Z87.1+
- ⚠️ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	23.62 x 14.76 x 16.73
Case Weight (lbs)	16.09
Country of Origin	Taiwan
Lens	Clear
Frame Style	Semi-Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	Anti-Scratch, Anti-Fog
Bridge	Rubber
Temple	Bayonet, Rubber Tips
Base Curve	9.5
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-07-28

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
250-33-0010	Black	Clear	Clear	AS/AR	616314130342	01616314130341	02616314130340
250-33-0020	Black	Clear	Clear	AS/AF	616314130328	01616314130327	02616314130326
250-33-0021	Black	Tinted	Gray	AS/AF	616314130335	01616314130334	02616314130333
250-33-0041	Black	Polarized	Gray	AS	616314130366	01616314130365	02616314130364
250-33-0226	Black	Indoor Outdoor Blue	Clear	AS/AF	616314130359	01616314130358	02616314130357
250-33-1010	Bronze	Clear	Clear	AS/AR	616314130397	01616314130396	02616314130395
250-33-1020	Bronze	Clear	Clear	AS/AF	616314130373	01616314130372	02616314130371
250-33-1024	Bronze	Tinted	Gray	AS/AF	616314130380	01616314130389	02616314130388
250-33-1226	Bronze	Indoor Outdoor Blue	Clear	AS/AF	616314130403	01616314130402	02616314130401

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated