Burst | E25088-142BK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Clusters of glass globes in various sizes and color are suspended from a central point and burst outward. Configurations include a 4-Light, 9-Light, and 12-Light cluster and can be mounted close to the ceiling or included down rods to extend the height. Choose from options of Clear or Frosted glass globe clusters paired with Satin Nickel frames for an airy transitional design or be bold with Mirror Smoked glass or a varied combination of the glass including amber tinted suspended on a Matte Black frame with thin black cables. Small-scaled LED G4 lamps are included with the fixtures and centered in the glass accentuating the scale of the glass.



*max overall height

MEASUREMENTS

DIMENSION	: 35.25" L x 35.25" W x 59.25" H
MAX OAH	: 103" OAH
CANOPY	: 6" W x 0.75" H x 6" L
HANGING WEIGHT	: 15.8 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 3,600 Rated (2,520 Del.)
BULB	: 2 x 1.8W LED G4 , 36W Total
BULB INCLUDED	: (Included)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)
Gold (GLD)

GLASS

Graduating Smoke 142

MATERIAL

Steel,Glass

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 25000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com