

ISAAC

B4203-PBR

The industrial-inspired Isaac features an elongated, tubular head and thoughtfully designed hardware details. With integrated LED and three pivot points, this picture light ensures both high efficiency and adjustability. The slim silhouette enhances a space without distracting from your artwork. Isaac is available in two sizes and two finishes, Patina Brass and Bronze.

FINISHES

PATINA BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 3.25"

Width/Diameter: 16"

Canopy/Backplate: 5.5"

Product Weight: 2.2lb

Extension: 8.5"

Top to Center: 1.25"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: Yes

Shade



ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Bulb Type: LED

Max Wattage: 10

Bulb Quantity: 1

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Dimmer Type: ELV, TRIAC

Gem Box Required (2"x3"): Yes

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 250

Title 24: No

Field Serviceable: No

SHIPPING

Carton 1: 20" x 12" x 7"

Carton 1 Weight: 4lb

Shipping Method: Ground

Country of Origin: VN