



## Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	20 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	1P
Short Circuit Current Rating	10 kA
Number of Spaces	1
Circuit Breaker Type	Tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	AWG 14...AWG 8 aluminium/copper)1
Type of Packing	Consumer packaging

## Complementary

Tightening torque	35.40 lbf.in (4.0 N.m) 0.00...0.01 in <sup>2</sup> (2.5...6 mm <sup>2</sup> ) (AWG 14...AWG 8)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)

## Environment

Ambient Air Temperature for Operation	104 °F (40 °C)
---------------------------------------	----------------

## Ordering and shipping details

Category	01322-HOMELINE TANDEM BLK/CARDED
Discount Schedule	CPH
GTIN	047569071065
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	6.40 oz (181.437 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	3.20 in (8.128 cm)
Package 2 Width	3.00 in (7.62 cm)
Package 2 Length	10.20 in (25.908 cm)
Package 2 Weight	4.55 lb(US) (2.064 kg)

Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	10.70 in (27.178 cm)
Package 3 Width	7.90 in (20.066 cm)
Package 3 Length	17.40 in (44.196 cm)
Package 3 Weight	46.20 lb(US) (20.956 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>