Loop | E23432-01PC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

A single loop of white tubing features an omnidirectional LED light. The full backplate can be mounted on a single gang junction box for a clean installation and is available in either Polished Chrome or Gold. A five-inch cover plate is included for installation on standard 4-0 junction boxes.



MEASUREMENTS

DIMENSION	: 3.25" L x 3.25" W x 24" H x 4" Ext
MAX OAH	: 24" W x 3.25" H
HANGING WEIGHT	: 3.08 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,020 Rated (800 Del.)
BULB	: 1 x 12W LED DC Integrated , 12W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Gold (GLD)

Polished Chrome (PC)

GLASS

White 01

MATERIAL

Steel, Acrylic

RATINGS

cETLus
Dry Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 50000 Hours
OPERATING TEMPERATURE: -20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com