

Insole for medium-high arches that makes your JALAS shoes even more comfortable and safe.

NEUTRALIZER 8710M MEDIUM ARCH

Learn more

MAKES YOUR MEDIUM-HIGH ARCHES HAPPY

The insole for medium arches makes your JALAS shoes more comfortable and safer. Poron® XRD® material in the forefoot and heel absorbs up to 90% of impact energy, providing outstanding shock absorption. This reduces injury risk and increases comfort. The insole is anatomically designed, ESD approved, and fits all JALAS safety shoes. Available in 17 sizes. Remove the original insoles before use. The JALAS FootStopService (FSS) scanner helps you choose the best insoles for your feet.

CHARACTERISTICS

- Perfect fit
- Extra comfortable
- Breathable
- Excellent shock absorption

FUNCTIONS

- ESD
- Anatomically designed
- Heel/arch support
- Perforated front section
- Medium height arch
- Double shock absorption zones
- Approved for use in all JALAS® protective shoes

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

jalas® NEUTRALIZER 8710M MEDIUM ARCH

PREVENTS RISK OF

Antistatic, Strain injuries

SPECIFICATION

TYPE Insoles
COLLECTION Neutralizer
MATERIAL Textile, Soft E.V.A, Polyester based electro conductive thread, Control bar in TPU, Double shock absorption zones in PORON® XRD®
COLOUR Green

COMPLIANCE FEATURES

Shock absorbing

Anti-static properties

ESD

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
34	1.5	2.5	3.5	8710M-34	6408487563720
35	2	3.5	4	8710M-35	6408487563782
36	3	4	5	8710M-36	6408487563843
37	4	5	6	8710M-37	6408487563904
38	5	5.5	6.5	8710M-38	6408487563966
39	6	6.5	7.5	8710M-39	6408487564024
40	6.5	7.5	8.5	8710M-40	6408487564086
41	7	8	9	8710M-41	6408487564147
42	8	9	10	8710M-42	6408487564208
43	9	9.5	11	8710M-43	6408487564260
44	10	10.5	11.5	8710M-44	6408487564321
45	10.5	11	12.5	8710M-45	6408487564383
46	11	12	13	8710M-46	6408487564444
47	12	13	14	8710M-47	6408487564505
48	13	13.5	14.5	8710M-48	6408487564567
49	14	14.5	15.5	8710M-49	6408487564628
50	15	15.5	16.5	8710M-50	6408487564680
34-35	1.5-2	2.5-3.5	3.5-4	8710M-34-35	6408487439445
36-37	3-4	4-5	5-6	8710M-36-37	6408487439452
48-50	13-15	13.5-15.5	14.5-16.5	8710M-48-50	6408487439513

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.