

Project Name

Location

Prepared By



Notes

[www] 02-03-2023 00:00:00

General	
Status	Active
Watts	5.5W
Fluorescent Equivalent	13W
Volts	120V-277V
Ballast Type	Type B
Shape	PL
Base	2GX7 (4-Pin)
ANSI Base	2GX7
Finish	Frost
CCT (Kelvin)	2700K/3000K/3500K/4000K
Temperature	Warm to Cool White
CRI	80
Lumens	600L/620L/630L/650L
Beam Spread	120
Dimmable	Non-Dimmable
Hours Rated	50000
Operating Position	Universal
Technology	LED

Electrical	
Ballasting Requirements	Ballast Bypass
Operating Frequency	50/60Hz
Power Factor	0.9
THD	20%
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical	
MOL	6.51
MOD	1.26
Weight (lb.)	0.07

Additional Information	
Rated For Enclosed Fixture	No
Warranty	5 Year Limited - 10 hr per day

Compliance	
Safety Listing	cULus - Classified
Location Rating	Damp
DLC Approved	No
NSF Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes