

LANE

B1617-PBR/CLC

Employing a graphic design language, the Lane sconce merges antique and machine-led details. The racetrack ceramic reflector frames the light source, which appears to float in the center of the dish. The white crackle glaze on the ceramic lends a textured, aged quality to the fixture, while the Patina Brass metalwork is industrial yet warm.

FINISHES

PATINA BRASS w/ CERAMIC WHITE LARGE
CRACKLE

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 16.5"

Width/Diameter: 4"

Canopy/Backplate: 2.25"

Product Weight: 4.4lb

Extension: 2.5"

Top to Center: 8.25"

Canopy/Backplate Shape: Rectangle

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: T8-3.5

Max Wattage: 10

Bulb Quantity: 2

Bulb Included: No

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): Yes

Dark Sky: No

SHIPPING

Carton 1: 22" x 9" x 8"

Carton 1 Weight: 8lb

Shipping Method: Ground

Country of Origin: PH

